

Pass Through Glass Washer

The Pass Through Glass Washer uses a rack to hold the bottles and has a dedicated nozzle rack to ensure that water goes directly into the bottle. This guarantees that each bottle is thoroughly cleaned and sanitised. There is also a rotating wash arm that goes around the top to clean the outside of the bottles.

Reliable
and
Robust
Design



Product features

- Thermostop system that meet HACCP requirements
- Hood operated start/stop functions option
- Wash/rinse arm with easy to remove & clean nozzles
- Door safety switch
- Break tank for council regulations
- Deep formed double skinned tank rounded tanks
- Full scrap screens
- Built in rinse aid/sanitiser & detergent pump
- Easy access for maintenance
- Temperature displayed
- Fully automatic process
- Self cleaning vertical pumps
- Double tank filters



Rhima Australia Pty Ltd

72-74 Woodlands Drive, Braeside Victoria 3195
www.rhima.com.au